

559089-2

Fiber Optic Termination Panel, 3 RU, 19 in, unloaded, 72 ports, black

Body Features

Chassis Color	Black
Finish	Powder coated

Configuration Features

Number of Ports	72
Configuration	Unloaded
Number of Fibers	12-72 72
Number of Splice Organizer Trays	6

Dimensions

Height	133.350 mm 5.250 in
Width	482.600 mm 19.000 in

Packaging Features

Includes	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Availability

Region	Asia Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Fiber Termination Panel
System	AMP NETCONNECT
Rack Units	3.0

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU	Classification Compliant
----------------------------------	------------------------------------