

569875-1

Modular Plug Snagless Boot for Category 5E and 5 Plugs, 5.33 mm, black



This product will be discontinued on: July 1, 2017

Replaced By:

MP-5EU-Boot-57-10
2843048-1

Modular Plug Boot, 8-Position Plugs, Slim-line, Transparent, 5.7mm Max Cable OD

Body Features

Color	Black
Boot Type	Snagless

Configuration Features

Number of Positions	8
---------------------	---

Dimensions

Cable Jacket Outside Diameter Range 0.21 in | 5.33 mm

Operation/Application

For Cable Diameter	5.33 mm 0.21 in
--------------------	-------------------

Other

Comment	Maximum Cable Diameter is 0.21 inches (5.33 mm) Use with Unshielded Cat 3, 5 or 5e Plugs.
---------	---

Packaging Features

Packaging Method	Carton
Packaging Quantity	1000

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Product Type	Accessory
Shielded	No
Accessory Type	Boot

569875-1

Performance Category	Category 3		Category 5		Category 5e
System	AMP NETCONNECT				

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant