

569877-5

Modular Plug Snagless Boot for Category 5E and 5 Plugs, 6.35 mm, blue



This product will be discontinued on: July 1, 2017

Replaced By:

MP-5EU-Boot-62-10
2111797-1

Modular Plug Boot, 8-Position Plugs, Slim-line, Transparent, 6.2mm Max Cable OD

Body Features

Color	Blue
Boot Type	Snagless

Configuration Features

Number of Positions	8
---------------------	---

Dimensions

Cable Jacket Outside Diameter Range 0.25 in | 6.35 mm

Operation/Application

For Cable Diameter	6.35 mm 0.25 in
--------------------	-------------------

Other

Comment	Maximum Cable Diameter is 0.250 inches (6.35 mm) Use with Unshielded Cat 3, 5 or 5e Plugs.
---------	--

Packaging Features

Packaging Method	Carton
------------------	--------

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Product Type	Accessory
Shielded	Yes
Accessory Type	Boot

569877-5

Performance Category	Category 3		Category 5		Category 5e
System	AMP NETCONNECT				

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant