

569877-6

**Modular Plug Snagless Boot for Category 5E and 5 Plugs, 6.35 mm, yellow**



**This product will be discontinued on: July 1, 2017**

**Replaced By:**

MP-5EU-Boot-62-10  
2111797-1

Modular Plug Boot, 8-Position Plugs, Slim-line, Transparent, 6.2mm Max Cable OD

## Body Features

Color	Yellow
Boot Type	Snagless

## Configuration Features

Number of Positions	8
---------------------	---

## Dimensions

Cable Jacket Outside Diameter Range 0.25 in | 6.35 mm

## Operation/Application

For Cable Diameter	6.35 mm   0.25 in
--------------------	-------------------

## Other

Comment	Maximum Cable Diameter is 0.250 inches (6.35 mm)   Use with Unshielded Cat 3, 5 or 5e Plugs.
---------	--

## Packaging Features

Packaging Method	Carton
------------------	--------

## Product Availability

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

## Product Type Features

Product Type	Accessory
Shielded	Yes
Accessory Type	Boot

569877-6

Performance Category	Category 3		Category 5		Category 5e
System	AMP NETCONNECT				

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant