
Product Specifications





6-1427200-4 Copper Cable, category 6, 4 pair, UTP, CMR rated, 23 AWG, 1000 ft reel-in-box, gray

Body Features

Jacket Material	PVC
Jacket Color	Gray
Conductor Material	Solid bare copper
Insulation Material	PE

Configuration Features

Dimensions

Overall Outside Diameter	6.400 mm	l	0.252 in
Length	305.00 m		1000.66 ft
Wire Size (CMA)	23 AWG		

Electrical Specifications

ANSI/TIA Category	6		
General Specification			
Cable Type	U/UTP (unshielded)		
Cable Type Industry Standards			

Packaging Features

Packaging Method

Reel-in-a-Box

Product Availability

Region

Asia | EMEA

Product Type Features

Cable Style	Multi-Pair
Cable Type	Twisted Pair
Product Classification	Cable - TIA/EIA Category
Product Type	Cable
Shielded	No

Product Specifications



6-1427200-4

SystemAMP NETCONNECTWire/Cable TypeTwisted Pair

Usage Conditions

Operating Temperature Range -20 - 60 °C | -4 - 140 °F

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU **Classification** Compliant