

**6278080-2****LightCrimp Plus™ Fiber Optic Connector Kit, SC, MM, duplex**

Body Features

Boot Color	Black
Coating/Buffer Size	250 µm 900 µm
Epoxyless	Yes
Protective Cap	Yes
Strain Relief Material	Thermoplastic elastomer (TPE)

Dimensions

Cable Outer Diameter	2.5 – 3 mm
----------------------	------------

Housing Features

Housing Color	Beige
Housing Material	Glass filled PBT

Identification Marking

AMP Logo	Yes
----------	-----

Packaging Features

Packaging Method	Package
Packaging Quantity	10

Product Availability

Region	Asia Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Connector
Connector Type	SC UPC
Optical Mode	Multimode
Cable Type	Buffered Fiber Coated Fiber Jacketed Cable
Connector Style	Duplex
Fiber Type	OM2
System	AMP NETCONNECT LIGHTCRIMP PLUS
Connector Design	One-Piece
Ferrule Material	Ceramic
Fiber Cable Buffering	Easy strip buffer
Fiber Diameter	50/125 µm
Pre-Polished	Yes
Strain Relief	Yes

6278080-2

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant