

6536464-2

**Fiber Optic Patch Cord, OM3, SC to SC, duplex, 2.5 mm zipcord, 2 m**

## Body Features

Cable Color	Aqua
Boot Color (End A)	Beige
Boot Color (End B)	Beige
Boot Type (End A)	Short
Boot Type (End B)	Short
Connector Color (End A)	Beige
Connector Color (End B)	Beige

## Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

## Dimensions

Assembly Length	2.00 m		6.56 ft
Cable Outer Diameter	.098 in		2.5 mm

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Product Availability

Region	Asia		Australia/New Zealand		EMEA		Latin America		North America
--------	------	--	-----------------------	--	------	--	---------------	--	---------------

## Product Type Features

Product Type	Patch Cord (duplex)
System	AMP NETCONNECT
Connector Type (End A)	SC/UPC
Connector Type (End B)	SC/UPC
Fiber Type	OM3
Fiber Diameter	50/125 µm
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Semi-tight buffer
Fiber Cable Type	Duplex, dualzip
Optical Mode	Multimode
Polarity	Pair Flipped

## Signal Characteristics

Return Loss, minimum	25 dB
----------------------	-------

6536464-2

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant

## \* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---