

**6536501-1****Fiber Optic Patch Cord, singlemode, 1.8 mm zipcord, LC/PC to LC/PC duplex tuned, 1 m**

## Body Features

Cable Color	Yellow
Boot Color (End A)	Blue
Boot Color (End B)	Blue
Boot Type (End A)	Bend limiting
Boot Type (End B)	Bend limiting
Connector Color (End A)	Blue
Connector Color (End B)	Blue

## Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

## Dimensions

Assembly Length	1.00 m   3.28 ft
Cable Outer Diameter	.071 in   1.8 mm

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Product Availability

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

## Product Type Features

Product Type	Patch Cord (duplex)
System	AMP NETCONNECT
Connector Type (End A)	LC/UPC
Connector Type (End B)	LC/UPC
Fiber Type	OS2
Fiber Diameter	9/125 µm
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer

6536501-1

Fiber Cable Type	Duplex, dualzip
Optical Mode	Singlemode
Polarity	Pair Flipped

## Signal Characteristics

Return Loss, minimum	45 dB
----------------------	-------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant

## \* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---