

6536502-5

**Fiber Optic Patch Cord, multimode, LC to LC, duplex, 1.8 mm zipcord, 5 m**

## Body Features

Cable Color	Orange
Boot Color (End A)	Beige
Boot Color (End B)	Beige
Boot Type (End A)	Bend limiting
Boot Type (End B)	Bend limiting
Connector Color (End A)	Beige
Connector Color (End B)	Beige

## Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

## Dimensions

Assembly Length	5.00 m   16.40 ft
Cable Outer Diameter	.071 in   1.8 mm

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Product Availability

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

## Product Type Features

Product Type	Patch Cord (duplex)
System	AMP NETCONNECT
Connector Type (End A)	LC/UPC
Connector Type (End B)	LC/UPC
Fiber Type	OM2
Fiber Diameter	50/125 µm
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Fiber Cable Type	Duplex, dualzip
Optical Mode	Multimode
Polarity	Pair Flipped

## Signal Characteristics

Insertion Loss, maximum (End A)	0.30 dB
---------------------------------	---------

6536502-5

Insertion Loss, maximum (End B) 0.30 dB

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

## \* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---