

6695121-3

Fiber Optic Patch Cord, multimode, 1.8 mm zipcord, LC duplex-ST, 3 m

OBSOLETE

This product was discontinued on: October 1, 2016

Body Features

Cable Color	Gray
Boot Color (End A)	Beige
Boot Color (End B)	Red/Black
Boot Type (End A)	Bend limiting
Boot Type (End B)	Push-on
Connector Color (End A)	Beige

Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2

Dimensions

Assembly Length	3.00 m 9.84 ft
Cable Outer Diameter	1.8 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Patch Cord (duplex)
System	AMP NETCONNECT
Connector Type (End A)	LC/UPC
Connector Type (End B)	ST/UPC
Fiber Type	OM1
Fiber Diameter	62.5/125 μ m
Connector Style (End A)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Fiber Cable Type	Duplex, dualzip
Optical Mode	Multimode

Regulatory Compliance/Certifications

Product Specifications



6695121-3

Agency

RoHS 2011/65/EU

Classification

Compliant

*** Footnotes**

Assembly Length	Assembly length includes the breakout lengths
-----------------	---