

6754402-2

**Fiber Optic Pigtail 1F, OM3, MM**

## Body Features

Cable Color	Aqua
Boot Color (End A)	Beige
Boot Type (End A)	Bend limiting
Connector Color (End A)	Beige

## Configuration Features

Number of Fibers	1
Number of Connectors (End A)	1
Number of Connectors (End B)	0
Exit Angle to Exit Angle	180° to pigtail

## Dimensions

Assembly Length	2.00 m   6.56 ft
Cable Outer Diameter	.079 in   2 mm

## Industry Standards

Flammability Rating	OFNR (Riser) Jacket
---------------------	---------------------

## Product Availability

Region	Asia   Latin America   North America
--------	--------------------------------------

## Product Type Features

Product Type	Pigtail
System	AMP NETCONNECT
Connector Type (End A)	LC/UPC
Connector Type (End B)	Stub Tail
Fiber Type	OM3
Fiber Diameter	50/125 µm
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Optical Mode	Multimode
Polarity	Pair Flipped

## Signal Characteristics

Insertion Loss, maximum (End A)	0.50 dB
---------------------------------	---------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

### \* Footnotes

6754402-2

---

Assembly Length	Assembly length includes the breakout lengths
-----------------	---