

6754485-4

LightCrimp Plus™ Fiber Optic Connector Kit

Body Features

Boot Color	Aqua
Boot Type	Short
Connector Color	Beige
Epoxyless	Yes

Dimensions

Boot Length	10.25 mm 0.40 in
Cable Outer Diameter	.0098 – .035 in .25 – .9 mm

Operation/Application

SECURE	No
--------	----

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Availability

Region	Asia Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Connector
Connector Type	LC UPC
Optical Mode	Multimode
Cable Type	Buffered Fiber
Connector Style	Duplex
Fiber Type	OM3/OM4
System	AMP NETCONNECT
Fiber Diameter	50/125 µm
Pre-Polished	Yes

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant