



6830 1 835-06

RJ45 Modular Jack, KM8, category 6A, 110 Punchdown, UTP, blue

Body Features

Color	Blue
Insert Style	Unshielded

Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	Universal

Dimensions

Cable Diameter (Max)	1.6 mm 0.1 in
Insulated Conductor Outside Diameter	0.019–0.025 in 0.5–0.65 mm
Wire Size (CMA)	.2 – .35 mm²

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Availability

Region	North America
--------	---------------

Product Type Features

Product Type	Modular Jack
Performance Category	Category 6A
Cable Type	UTP
Connector Style	Jack
Connector Type	RJ45
Dust Cover	No

Termination Features

Termination Method	110 Punchdown IDC
--------------------	---------------------

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

Product Specifications



6830 | 835-06

RoHS 2011/65/EU

Compliant