



8-2055711-0

**MPO Trunk Cable, 12 fiber, singlemode, MPO female-female, LSZH, straight, 80 m**

## Body Features

Cable Color	Yellow
Boot Color (End A)	Black
Boot Color (End B)	Black
Boot Type (End B)	Standard
Connector Color (End A)	Green
Connector Color (End B)	Green

## Configuration Features

Number of Fibers	12
Number of Connectors (End A)	1
Number of Connectors (End B)	1
Exit Angle to Exit Angle	180° to 180°

## Dimensions

Assembly Length	80.00 m   262.47 ft
Cable Outer Diameter	.251 in   6.4 mm

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Product Availability

Region	Australia/New Zealand   EMEA
--------	------------------------------

## Product Type Features

Product Type	Trunk cable
System	AMP NETCONNECT
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OS2
Fiber Diameter	9/125 μm
Ferrule Material	Thermoplastic
Fiber Cable Buffering	Loose tube
Optical Mode	Singlemode
Polarity	Straight

## Signal Characteristics

8-2055711-0

Return Loss, minimum            35 dB

---

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant

---

### \* Footnotes

Assembly Length            Assembly length includes the breakout lengths