



9-2160136-2  
MPOptimate® Trunk Cable, 12 fiber, female-female, OM4, straight, 2.5 m

## Body Features

Cable Color                      Aqua

## Configuration Features

Number of Fibers                      12  
Number of Connectors (End A)   1  
Number of Connectors (End B)   1

## Dimensions

Assembly Length                      2.50 m   |   8.20 ft

## Product Availability

Region                                  Australia/New Zealand   |   EMEA

## Product Type Features

Product Type                      Trunk cable  
System                              AMP NETCONNECT   |   MPOptimate®  
Connector Type (End A)           MPO  
Connector Type (End B)           MPO  
Fiber Type                          OM4  
Fiber Diameter                      50/125 µm  
Optical Mode                        Multimode

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

## \* Footnotes

Assembly Length                      Assembly length includes the breakout lengths