



959309-1

RJ45 Patch Cord, category 5e, F/UTP, stranded, red, 1 m

Body Features

Cable Color	Red
Shield Style	F/UTP
Conductor Material	Copper
Conductor Type	Stranded

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Power Positions	0

Dimensions

Length	1.00 m 3.28 ft
Overall Outside Cable Diameter	5.600 mm 0.220 in
Wire Size (CMA)	.129 mm ² 26 AWG

Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

Operation/Application

Halogen Free	Yes
--------------	-----

Packaging Features

Packaging Method	Bag
------------------	-----

Product Availability

Region	EMEA
--------	------

Product Type Features

Product Type	Patch Cord
System	AMP NETCONNECT
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Category 5e
Cable Assembly Category	Industry Standard

959309-1

Shielded Yes

Usage Conditions

Operating Temperature Range -20 – 60 °C

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant