

**959385-2****RJ45 Patch Cord, category 6, shielded, white, 2 m**

Body Features

| | |
|--------------------|----------|
| Cable Color | White |
| Shield Style | S/FTP |
| Conductor Material | Copper |
| Conductor Type | Stranded |

Configuration Features

| | |
|---------------------------|--------------|
| Configuration | Double-ended |
| Keyed | No |
| Number of Positions | 4-pair |
| Number of Power Positions | 0 |

Dimensions

| | |
|--------------------------------|-------------------------------|
| Length | 2.00 m 6.56 ft |
| Overall Outside Cable Diameter | 5.900 mm 0.232 in |
| Wire Size (CMA) | .129 mm ² 26 AWG |

Industry Standards

| | |
|---------------------|-------------------------------|
| Flammability Rating | LSZH (Low Smoke Zero Halogen) |
|---------------------|-------------------------------|

Operation/Application

| | |
|--------------|----|
| Halogen Free | No |
|--------------|----|

Packaging Features

| | |
|------------------|-----|
| Packaging Method | Bag |
|------------------|-----|

Product Availability

| | |
|--------|------|
| Region | EMEA |
|--------|------|

Product Type Features

| | |
|-------------------------|-------------------|
| Product Type | Patch Cord |
| System | AMP NETCONNECT |
| Assembly Type | Plug to Plug |
| Connector Type (End A) | RJ45 Modular Plug |
| Connector Type (End B) | RJ45 Modular Plug |
| Performance Category | Category 6 |
| Cable Assembly Category | Industry Standard |

Product Specifications



959385-2

Shielded Yes

Usage Conditions

Operating Temperature Range -20 – 60 °C

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant