



SRS-ELMN-DN45-YL-A

SpeedPRO™ Vertical Elbow, 45° down, 100 mm x 100 mm (4 in x 4 in), yellow

## OBSOLETE

This product was discontinued on: May 1, 2016

### Dimensions

System Dimensions	100 mm x 100 mm		4 in x 4 in
Height	129.0 mm		5.1 in
Length	101.0 mm		4.0 in
Width	106.0 mm		4.2 in

### Environmental Specifications

Flammability Rating	UL 94 V-0
Halogen Characteristics	LSZH
Safety Standard	UL

### General Specifications

Section Type	Elbow section
Color	Yellow
Orientation	Vertical
Angle/Bend Direction	45° down
Brand	SpeedPRO™
Minimum Order Quantity	1
Package Quantity	1
Product Type	Channel
Warranty	20 years

### Mechanical Specifications

Material Type	PPO/PS
---------------	--------

### Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

# Product Specifications



SRS-EI/MN-DN45-YL-A

