



SRS-ELMN-DN45-YL-F
SpeedPRO™ Vertical Elbow, 45° down, 300 mm x 100 mm (12 in x 4 in), yellow

OBSOLETE
This product was discontinued on: May 1, 2016

Dimensions

| | | | |
|-------------------|--------------|--|-----------------|
| System Dimensions | 12 in x 4 in | | 300 mm x 100 mm |
| Height | 145.0 mm | | 5.7 in |
| Length | 101.0 mm | | 4.0 in |
| Width | 306.0 mm | | 12.0 in |
| Weight | 0.18 kg | | 0.39 lb |

Environmental Specifications

| | |
|-------------------------|-----------|
| Flammability Rating | UL 94 V-0 |
| Halogen Characteristics | LSZH |
| Safety Standard | UL |

General Specifications

| | |
|------------------------|---------------|
| Section Type | Elbow section |
| Color | Yellow |
| Orientation | Vertical |
| Angle/Bend Direction | 45° down |
| Brand | SpeedPRO™ |
| Minimum Order Quantity | 1 |
| Package Quantity | 1 |
| Product Type | Channel |
| Warranty | 20 years |

Mechanical Specifications

| | |
|---------------|--------|
| Material Type | PPO/PS |
|---------------|--------|

Regulatory Compliance/Certifications

| | |
|----------------------------------|------------------------------------|
| Agency RoHS 2011/65/EU | Classification Compliant |
|----------------------------------|------------------------------------|

