



SRS-ELMN-UP30-YL-A

SpeedPRO™ Vertical Elbow, 30° up, 100 mm x 100 mm (4 in x 4 in), yellow

OBSOLETE

This product was discontinued on: May 1, 2016

Dimensions

System Dimensions	100 mm x 100 mm		4 in x 4 in
Height	91.0 mm		3.6 in
Length	101.0 mm		4.0 in
Width	106.0 mm		4.2 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Halogen Characteristics	LSZH
Safety Standard	UL

General Specifications

Section Type	Elbow section
Color	Yellow
Orientation	Vertical
Angle/Bend Direction	30° up
Brand	SpeedPRO™
Minimum Order Quantity	1
Package Quantity	1
Product Type	Channel
Warranty	20 years

Mechanical Specifications

Material Type	PPO/PS
---------------	--------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

Product Specifications



SRS-EL/MN-UP30-YL-A

