

**SRS-STHT-SLNU-YL-A****SpeedPRO™ Straight Slotted Channel with hinged cover, 100 mm x 100 mm (4 in x 4 in), 2 m (6 ft 6 in) length, yellow****OBSOLETE****This product was discontinued on: May 1, 2016**

Dimensions

System Dimensions	100 mm x 100 mm 4 in x 4 in
Height	122.0 mm 4.8 in
Length	2000.0 mm 78.7 in
Width	120.0 mm 4.7 in
Weight	3.30 kg 7.28 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Halogen Characteristics	LSZH
Safety Standard	UL

General Specifications

Product Type	Channel with hinged cover
Color	Yellow
Brand	SpeedPRO™
Minimum Order Quantity	1
Package Quantity	1
Section Type	Straight section
Warranty	20 years

Mechanical Specifications

Material Type	PPO/PS
---------------	--------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU**Classification**
Compliant