



SRS-STMN-NUNU-BK-A

SpeedPRO™ Straight Solid Channel, 100 mm x 100 mm (4 in x 4 in), 2 m (6 ft 6 in) length, black

OBSOLETE

This product was discontinued on: May 1, 2016

Replaced By:

FGSB-MSHS-A
1434956

FiberGuide® Straight Solid Channel, 100 mm x 100 mm (4 in x 4 in), 1.83 m (6 ft) length, black

Dimensions

System Dimensions	100 mm x 100 mm 4 in x 4 in
Height	112.0 mm 4.4 in
Length	2000.0 mm 78.7 in
Width	120.0 mm 4.7 in
Weight	2.02 kg 4.46 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Halogen Characteristics	LSZH
Safety Standard	UL

General Specifications

Product Type	Solid channel
Color	Black
Brand	SpeedPRO™
Minimum Order Quantity	1
Package Quantity	1
Section Type	Straight section
Warranty	20 years

Mechanical Specifications

Material Type	PPO/PS
---------------	--------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

