

# Non-Contact Phase Sequence Tester

**Checks phase sequence and phase status**

*Tests up to 1000VAC with LED and audible indication*

## Features:

- 75 to 1000VAC input voltage with 45 to 65Hz frequency range
- LEDs indicate phase orientation (clockwise or counter-clockwise) and whether each phase is live
- Beeper sounds intermittently when correct phase is detected and continuously if phase is reversed
- Durable housing with back cover magnet for attachment to an AC distribution panel for easy measurement
- Adjustable Hi/Lo LED brightness switch for making measurements in dimly lit areas or sunlight
- Fully insulated alligator clips with wide jaws
- Low battery warning
- CAT IV-600V safety rating
- Dimensions: 4.7 x 2.7 x 1.5" (118 x 69 x 38mm); Weight: 13oz (370g)
- Complete with three built-in 30" test leads with large color-coded alligator clips, four AA batteries, and pouch case



## Ordering Information:

PRT200 .....Non-Contact Phase Sequence Tester

