

ACS150-03E-07A3-4



Products Drives Low voltage AC drives Micro drives

General Information

Global Commercial Alias:	ACS150-03E-07A3-4
Product ID:	68581800
ABB Type Designation:	ACS150-03E-07A3-4
EAN:	6410038079482
Catalog Description:	IP20; 3 phase;

Additional Information

ABB Type Designation:	ACS150-03E-07A3-4
Country of Origin:	China (CN) Finland (FI)
Customs Tariff Number:	85044084
EAN:	6410038079482
Enclosure Class:	IP20
Frequency (f):	48 ... 63 Hz
Gross Weight:	1.9 kg
Input Voltage (U _n):	380 ... 480 V
Invoice Description:	ACS150-03E-07A3-4 Pn 3,0kW, I2n 7,3A IP20
Made To Order:	No
Minimum Order Quantity:	1 piece
Mounting Type:	Cabinet / Wall mounting
Number of Phases:	3
Order Multiple:	1 piece
Output Current, Light-Overload Use:	7.3 A
Output Current, Normal Use:	7.3 A
Output Power, Light-Overload Use:	3 kW 3 Hp
Output Power, Normal Use:	3 kW 3 Hp
Product Main Type:	ACS150
Product Name:	Frequency converter
Product Net Height:	344 mm
Product Net Length:	217 mm
Product Net Weight:	1.4 kg
Product Net Width:	132 mm
Product Series:	ACS150
Quote Only:	No
Selling Unit of Measure:	piece
Stocked At (Warehouses):	Central Stock Europe Central Stock Asia FIPSEEXPU FIPSEEXPU014 SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU
Global Commercial Alias:	ACS150-03E-07A3-4

