

General Information

Extended Product Type:	332MVS3W
Product ID:	2CMA167876R1000
EAN:	7392696678766
Catalog Description:	Switched interlocked socket-outlet, 3h, 32A, IP67, 3P+E
Long Description:	Switched Interlocked Socket Outlet, vertical, earthing sleeve position 3h, rated current 32A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code red

Additional Information

Additional Information:	3P+E
Cable Cross-Section:	2.5 ... 10 mm ²
Cable Entry Position:	Top
Cable Outlets Per Side:	1xØ25
Color:	Red
Connection Type:	Screw clamp
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85366990
Data Sheet, Technical Information:	2CMC700014C0008
Declaration:	2CMC700005D0001
Declaration of Conformity - CE:	2CMC700005D0001
Degree of Protection:	acc. to IEC 60529 IP67
E-nummer:	removed
EAN:	7392696678766
ETIM 4:	EC001324 - CEE socket outlet, disconnectable, with fuse
ETIM 5:	EC000140 - CEE plug
ETIM 6:	EC001321 - CEE socket outlet
Enclosure Material:	Thermoplastic polyester (PBT)
Environmental Information:	2CMC700001D0002
Frequency (f):	50/60 Hz
Function:	Switched interlocked socket outlet, vertical
Gross Weight:	0.8 kg
Housing Material:	Thermoplastic (PBT)
IIT Publishing Status:	Level 0 - Information enabled
Instructions and Manuals:	2CMC700002D0001
Invoice Description:	Ind. P&S#332MVS3W
Minimum Order Quantity:	1 piece
Mounting Type:	Vertical
Number of Poles:	4
Object Classification Code:	2CMT005069
Package Level 1 EAN:	7392696678766
Package Level 1 Gross Weight:	0.8 kg
Package Level 1 Height:	265 mm
Package Level 1 Length:	120 mm
Package Level 1 Units:	1 piece
Package Level 1 Width:	152 mm
Product Main Type:	CMVS

Product Name:	Industrial Switched Interlocked Socket Outlet
Product Net Depth:	243 mm
Product Net Height:	149 mm
Product Net Length:	243 mm
Product Net Weight:	0.72 kg
Product Net Width:	120 mm
Protection Type:	Switched Interlocked
Rated Current (I_n):	32 A
Rated Voltage (U_r):	380/440 V
RoHS Date:	L23
RoHS Information:	2CMC700057D0001
Selling Unit of Measure:	piece
Short Description:	Switched interlocked socket-outlet, 3h, 32A, IP67, 3P+E
Size:	149X120X253
Standards:	IEC 60309-1 IEC 60309-2 IEC 60309-4
Sub-Function:	Cable entry, knock-outs Ø25mm
Suitable For:	Switched Interlocked Socket Outlets, Vertical
Suitable for Product Class:	Industrial Plugs and Sockets
UNSPSC:	39120000
Clock Position Of Grounding Contact:	3 hour
RAL Number:	RAL 7001 - Silver Grey

