

# RD2



Products Low Voltage Products and Systems Modular DIN Rail Products Modular DIN Rail Components MDRCs  
Residual Current Monitors, RCMs

## General Information

<b>Extended Product Type:</b>	RD2
<b>Product ID:</b>	2CSM142120R1201
<b>EAN:</b>	8012542058007
<b>Catalog Description:</b>	RD2 Residual Current Monitor
<b>Long Description:</b>	Residual current monitors (RCMs) with external transformer can detect leakage currents. Through minidip you can set sensitivity and intervention time. Operating voltage: 230...400V a.c.

## Additional Information

Country of Origin:	Hungary (HU)
Customs Tariff Number:	85364190
Data Sheet, Technical Information:	2CSC400002D0209
Declaration of Conformity - CE:	2CSC444006D2701
Dimensions:	2 modules
E-nummer:	2161640
EAN:	8012542058007
ETIM 4:	EC001445 - Residual current monitoring relay
ETIM 5:	EC001445 - Residual current monitoring relay
ETIM 6:	EC001445 - Residual current monitoring relay
Environmental Information:	2CSM444001E0201
Filter Option:	no frequency filter
Instructions and Manuals:	2CSM444001D5901
Invoice Description:	RD2 Residual Current Monitor
Minimum Order Quantity:	1 piece
Mounting Type:	DIN-rail
Number of Contacts:	1
Object Classification Code:	Q
Options Provided:	Pre-alarm threshold: no
Package Level 1 EAN:	8012542058007
Package Level 1 Gross Weight:	0.15 kg
Package Level 1 Height:	0.08 m
Package Level 1 Length:	0.103 m
Package Level 1 Units:	1 piece
Package Level 1 Width:	0.041 m
Power Loss:	at Rated Operating Conditions per Pole 3.4 W
Product Main Type:	RD2
Product Name:	Residual Current Monitor
Product Net Depth:	0.065 m
Product Net Height:	0.085 m
Product Net Weight:	0.105 kg
Product Net Width:	0.035 m
Rated Operational Voltage:	230 ... 400 V AC
Selling Unit of Measure:	piece
Standards:	IEC EN 62020
Type of Residual Current:	A type