

ACS355-03E-04A1-4



Products Drives Low voltage AC drives Machinery drives

Parts & Services Drives Low voltage AC drives Machinery drives ACS355 - Machinery Drive

General Information

Global Commercial Alias:	ACS355-03E-04A1-4
Product ID:	3AUA0000058186
ABB Type Designation:	ACS355-03E-04A1-4
EAN:	6438177223610
Catalog Description:	IP20; 3 phase;

Additional Information

ABB Type Designation:	ACS355-03E-04A1-4
Country of Origin:	China (CN) Finland (FI)
Customs Tariff Number:	85044084
EAN:	6438177223610
Enclosure Class:	IP20
Frequency (f):	48 ... 63 Hz
Gross Weight:	2.2 kg
Input Voltage (U _{in}):	380 ... 480 V
Invoice Description:	ACS355-03E-04A1-4 Pn 1,5kW, I2n 4,1A IP20.
Made To Order:	No
Minimum Order Quantity:	1 piece
Mounting Type:	Wall-mounted
Number of Phases:	3
Order Multiple:	1 piece
Output Current, Normal Use:	4.1 A
Output Power, Normal Use:	1.5 kW 2.0 Hp
Product Main Type:	ACS355
Product Name:	Frequency converter
Product Net Height:	344 mm
Product Net Length:	217 mm
Product Net Weight:	1.7 kg
Product Net Width:	132 mm
Product Series:	ACS355
Quote Only:	No
Replaced Product ID (OLD):	68468132
Selling Unit of Measure:	piece
Stocked At (Warehouses):	Central Stock Europe Central Stock Asia FIPSEEXPU FIPSEEXPU014 SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU
Global Commercial Alias:	ACS355-03E-04A1-4

Where Used (as a spare part for "Products")

1 Products		Filter	
Identifier	Description	Qty	Unit Of Measure
ACS355-03E-04A1-4	No Description Available	1	piece

Product specific part data

1 Products		Filter	
Product	Category	Drive Part Category	
ACS355-03E-04A1-4	ACS355 - Machinery Drive	Drive, Supply and Power Modules	