

# ACS355-03E-12A5-4



Products   Drives   Low voltage AC drives   Machinery drives

Parts & Services   Drives   Low voltage AC drives   Machinery drives   ACS355 - Machinery Drive

## General Information

|                                 |                   |
|---------------------------------|-------------------|
| <b>Global Commercial Alias:</b> | ACS355-03E-12A5-4 |
| <b>Product ID:</b>              | 3AUA0000058190    |
| <b>ABB Type Designation:</b>    | ACS355-03E-12A5-4 |
| <b>EAN:</b>                     | 6438177223658     |
| <b>Catalog Description:</b>     | IP20; 3 phase;    |

Additional Information

|                                   |                                                                                                                                         |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| ABB Type Designation:             | ACS355-03E-12A5-4                                                                                                                       |
| Country of Origin:                | China (CN)<br>Finland (FI)                                                                                                              |
| Customs Tariff Number:            | 85044084                                                                                                                                |
| EAN:                              | 6438177223658                                                                                                                           |
| Enclosure Class:                  | IP20                                                                                                                                    |
| Frequency (f):                    | 48 ... 63 Hz                                                                                                                            |
| Gross Weight:                     | 3.7 kg                                                                                                                                  |
| Input Voltage (U <sub>in</sub> ): | 380 ... 480 V                                                                                                                           |
| Invoice Description:              | ACS355-03E-12A5-4 Pn 5,5kW, I2n 12,5A IP20                                                                                              |
| Made To Order:                    | No                                                                                                                                      |
| Minimum Order Quantity:           | 1 piece                                                                                                                                 |
| Mounting Type:                    | Wall-mounted                                                                                                                            |
| Number of Phases:                 | 3                                                                                                                                       |
| Order Multiple:                   | 1 piece                                                                                                                                 |
| Output Current, Normal Use:       | 12.5 A                                                                                                                                  |
| Output Power, Normal Use:         | 5.5 kW<br>7.5 Hp                                                                                                                        |
| Product Main Type:                | ACS355                                                                                                                                  |
| Product Name:                     | Frequency converter                                                                                                                     |
| Product Net Height:               | 344 mm                                                                                                                                  |
| Product Net Length:               | 217 mm                                                                                                                                  |
| Product Net Weight:               | 3.2 kg                                                                                                                                  |
| Product Net Width:                | 226 mm                                                                                                                                  |
| Product Series:                   | ACS355                                                                                                                                  |
| Quote Only:                       | No                                                                                                                                      |
| Replaced Product ID (OLD):        | 68468175                                                                                                                                |
| Selling Unit of Measure:          | piece                                                                                                                                   |
| Stocked At (Warehouses):          | Central Stock Europe<br>Central Stock Asia<br>FIPSEEXPU<br>FIPSEEXPU014<br>SGRDC002EXPU<br>CNIAB001EXPU<br>SGIND002EXPU<br>AUABB024EXPU |
| Global Commercial Alias:          | ACS355-03E-12A5-4                                                                                                                       |

Where Used (as a spare part for "Products")

| 1 Products        |                          | Filter |                 |
|-------------------|--------------------------|--------|-----------------|
| Identifier        | Description              | Qty    | Unit Of Measure |
| ACS355-03E-12A5-4 | No Description Available | 1      | piece           |

Product specific part data

| 1 Products        |                          | Filter                          |  |
|-------------------|--------------------------|---------------------------------|--|
| Product           | Category                 | Drive Part Category             |  |
| ACS355-03E-12A5-4 | ACS355 - Machinery Drive | Drive, Supply and Power Modules |  |