

ACS355-03E-23A1-4



[Products](#) [Drives](#) [Low voltage AC drives](#) [Machinery drives](#)

[Parts & Services](#) [Drives](#) [Low voltage AC drives](#) [Machinery drives](#) [ACS355 - Machinery Drive](#)

General Information

Global Commercial Alias:	ACS355-03E-23A1-4
Product ID:	3AUA0000058192
ABB Type Designation:	ACS355-03E-23A1-4
EAN:	6438177223672
Catalog Description:	IP20; 3 phase;

Additional Information

ABB Type Designation:	ACS355-03E-23A1-4
Country of Origin:	China (CN) Finland (FI)
Customs Tariff Number:	85044088
EAN:	6438177223672
Enclosure Class:	IP20
Frequency (f):	48 ... 63 Hz
Gross Weight:	4.1 kg
Input Voltage (U _{in}):	380 ... 480 V
Invoice Description:	ACS355-03E-23A1-4 Pn 11kW, I2n 23,1A IP20.
Made To Order:	No
Minimum Order Quantity:	1 piece
Mounting Type:	Wall-mounted
Number of Phases:	3
Order Multiple:	1 piece
Output Current, Normal Use:	23.1 A
Output Power, Normal Use:	11.0 kW 15.0 Hp
Product Main Type:	ACS355
Product Name:	Frequency converter
Product Net Height:	344 mm
Product Net Length:	217 mm
Product Net Weight:	3.6 kg
Product Net Width:	226 mm
Product Series:	ACS355
Quote Only:	No
Replaced Product ID (OLD):	68734347
Selling Unit of Measure:	piece
Stocked At (Warehouses):	Central Stock Europe Central Stock Asia FIPSEEXPU FIPSEEXPU014 SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU
Global Commercial Alias:	ACS355-03E-23A1-4

Where Used (as a spare part for "Products")

1 Products		Filter	
Identifier	Description	Qty	Unit Of Measure
ACS355-03E-23A1-4	No Description Available	1	piece

Product specific part data

1 Products		Filter	
Product	Category	Drive Part Category	
ACS355-03E-23A1-4	ACS355 - Machinery Drive	Drive, Supply and Power Modules	