

General Information

Extended Product Type:	HK4-11
Product ID:	1SAM401901R1001
EAN:	4013614265846
Catalog Description:	HK4-11 Auxiliary Contact
Long Description:	HK4-11 Auxiliary contact 1NO/1NC

Additional Information

Accessory Type:	Auxiliary Contact
Ambient Air Temperature:	Operation -25 ... +70 °C Storage -50 ... +80 °C
BV Certificate:	1SAA937000-0201
CCC Certificate:	1SAA937002-3803
Connecting Capacity Auxiliary Circuit UL/CSA:	Flexible 1/2x 18-14 AWG Stranded 1/2x 18-14 AWG
Connecting Capacity Auxiliary Circuit:	Flexible with Ferrule 1/2x 0.5 ... 1.5 mm ² Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible 1/2x 0.5 ... 1.5 mm ² Flexible 1/2x 0.75 ... 1 mm ² Rigid 1/2x 0.5 ... 1.5 mm ² Rigid 1/2x 0.75 ... 2.5 mm ²
Contact Rating UL/CSA:	C300 R300
Conventional Free-air Thermal Current (I_{th}):	2.5 A
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85369095
DNV Certificate:	1SAA937000-0301
Data Sheet, Technical Information:	1SBC100173C0201
Declaration of Conformity - CE:	1SAD938506-0050 1SAD938505-0051 1SAD938505-0050
Degree of Protection:	IP20
E-number:	3112302
EAN:	4013614265846
ETIM 4:	EC002498 - Accessories for low-voltage switch technology
ETIM 5:	EC000041 - Auxiliary contact block
ETIM 6:	EC000041 - Auxiliary contact block
GL Certificate:	1SAA937000-0404
GOST Certificate:	1SAA937000-2703
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Invoice Description:	HK4-11 Auxiliary contact 1NO/1NC
Maximum Operating Voltage UL/CSA:	Auxiliary Circuit 250 V AC/DC
Minimum Order Quantity:	1 piece
Number of Auxiliary Contacts CO (SPDT):	0
Number of Auxiliary Contacts NC:	1
Number of Auxiliary Contacts NO:	1
Package Level 1 Gross Weight:	0.017 kg

Package Level 1 Gross Weight:	0.017 kg
Package Level 1 Height:	106 mm
Package Level 1 Length:	50 mm
Package Level 1 Units:	10 piece
Package Level 1 Width:	46 mm
Product Main Type:	HK4
Product Name:	Auxiliary Contact
Product Net Depth:	35 mm
Product Net Height:	55 mm
Product Net Weight:	0.017 kg
Product Net Width:	16 mm
Rated Insulation Voltage (U _i):	300 V
Rated Operational Current AC-15 (I _e):	(230 V) 1 A (24 V) 2 A
Rated Operational Current DC-13 (I _e):	(24 V) 1 A (48 V) 0 A
Rated Operational Voltage:	230 V AC 220 V DC Main Circuit 230 V
Recommended Screw Driver:	Pozidriv 2
RoHS Date:	0066
RoHS Information:	1SAD938506-0050 1SAD938505-0051
RoHS Status:	Following EU Directive 2011/65/EC
Selling Unit of Measure:	piece
Short Description:	HK4-11 Auxiliary contact 1NO/1NC
Standards:	IEC/EN 60947-1 IEC/EN 60947-2 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 508 CSA 22.2 No. 14
Suitable For:	MS450 MS451 MO450 MS495 MS496 MS497 MO495 MO496
Suitable for Product Class:	Manual Motor Starter
Tightening Torque:	Auxiliary Circuit 0.8 ... 1.2 N·m
Tightening Torque UL/CSA:	Auxiliary Circuit 7 ... 10.3 in·lb
UL Certificate:	UL_E149922
UNSPSC:	39121500
Wire Stripping Length:	Auxiliary Circuit 10 mm
eClass:	7.0 27371302



