

Products Drives Drive options I/O options

Parts & Services Drives Low voltage AC drives Machinery drives ACS355 - Machinery Drive

General Information

Global Commercial Alias:	MREL-01
Product ID:	3AUA0000031854
ABB Type Designation:	MREL-01
EAN:	6410038040987
Catalog Description:	MREL-01; MREL-01, Relay Output Extension for ACS350

Additional Information

ABB Type Designation:	MREL-01
Country of Origin:	China (CN) Finland (FI)
Customs Tariff Number:	85049099
EAN:	6410038040987
Gross Weight:	0.12 kg
Invoice Description:	MREL-01, Relay Output Extension for ACS350
Made To Order:	No
Minimum Order Quantity:	1 piece
Order Multiple:	1 piece
Product Main Type:	ACS350
Product Name:	Extension modules
Product Net Height:	40 mm
Product Net Length:	165 mm
Product Net Weight:	0.1 kg
Product Net Width:	115 mm
Quote Only:	No
Selling Unit of Measure:	piece
Stocked At (Warehouses):	Central Stock Europe Central Stock Asia FIPSEEXPU FIPSEEXPU014 SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU
Global Commercial Alias:	MREL-01

Where Used (as a spare part for "Products")

30 Products		Filter		
Identifier	Description	Qty	Unit Of Measure	
ACS355-01E-02A4-2	No Description Available	1	piece	
ACS355-01E-04A7-2	No Description Available	1	piece	
ACS355-01E-06A7-2	No Description Available	1	piece	
ACS355-01E-07A5-2	No Description Available	1	piece	
ACS355-01E-09A8-2	No Description Available	1	piece	
ACS355-03E-01A2-4	No Description Available	1	piece	

Identifier	Description	Qty	Unit Of Measure
ACS355-03E-01A9-4	No Description Available	1	piece
ACS355-03E-02A4-2	No Description Available	1	piece
ACS355-03E-02A4-4	No Description Available	1	piece
ACS355-03E-03A3-4	No Description Available	1	piece
ACS355-03E-03A5-2	No Description Available	1	piece
ACS355-03E-04A1-4	No Description Available	1	piece
ACS355-03E-04A7-2	No Description Available	1	piece
ACS355-03E-05A6-4	No Description Available	1	piece
ACS355-03E-06A7-2	No Description Available	1	piece
ACS355-03E-07A3-4	No Description Available	1	piece
ACS355-03E-07A5-2	No Description Available	1	piece
ACS355-03E-08A8-4	No Description Available	1	piece
ACS355-03E-09A8-2	No Description Available	1	piece
ACS355-03E-12A5-4	No Description Available	1	piece
ACS355-03E-13A3-2	No Description Available	1	piece
ACS355-03E-15A6-4	No Description Available	1	piece
ACS355-03E-17A6-2	No Description Available	1	piece
ACS355-03E-23A1-4	No Description Available	1	piece
ACS355-03E-24A4-2	No Description Available	1	piece
ACS355-03E-31A0-2	No Description Available	1	piece
ACS355-03E-31A0-4	No Description Available	1	piece
ACS355-03E-38A0-4	No Description Available	1	piece
ACS355-03E-44A0-4	No Description Available	1	piece
ACS355-03E-46A2-2	No Description Available	1	piece

Product specific part data

30 Products

Filter

Product	Category	Drive Part Category
ACS355-01E-02A4-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-01E-04A7-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-01E-07A5-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-01E-09A8-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-01A2-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-01A9-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-02A4-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-02A4-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)

Product	Category	Drive Part Category
ACS355-03E-03A3-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-03A5-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-04A1-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-04A7-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-05A6-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-06A7-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-07A3-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-07A5-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-08A8-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-09A8-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-13A3-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-17A6-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-31A0-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-38A0-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-44A0-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-46A2-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-01E-06A7-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-12A5-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-15A6-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-23A1-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-24A4-2	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)
ACS355-03E-31A0-4	ACS355 - Machinery Drive	Interface Option (Fieldbus, I/O etc.)