



760207274 | M2000-1U
M2000 MODULAR PANEL – 1U

Dimensions

Depth	119.38 mm 4.70 in
Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in
Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	5e 6 6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Total Ports, quantity	24
Cable Type	U/UTP (unshielded)
Product Type	Panel
Brand	CommScope®
Color	Black
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	1

Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
Wiring	T568A T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMScope®

760207274 | M2000-1U

