



SPECTRUM 4® CHAIN



- Carbon Steel.
- Minimum Ultimate load is 3 times the Working Load Limit.
- Proof Tested at 1.5 times the Working Load Limit with certification.
- Permanently embossed with CG® (Crosby Group) and 7 (Grade).
- Finish - Self Colored
- Standard container - fiber drum.

SPECTRUM 4® High Test Chain

Chain Size (in.)	Working Load Limit (lbs.)*	Feet Per Drum	Weight Per 100 Feet (lbs.)	Drum Stock No.	1/2 Drum Stock No.
1/4	2600	800	70	272788	272895
5/16	3900	550	106	272797	272902
3/8	5400	400	154	272804	272911
7/16	7200	300	209	272813	272920
1/2	9200	200	267	272822	272939
5/8	13000	150	402	272831	272948
3/4	20200	100	567	272840	272957

* Proof Loaded at 1.5 times the Working Load Limit.



NOTE : * Spectrum 4® High Test Chain is not recommended for overhead lifting. For these applications, Spectrum 8® or Spectrum 10® Alloy chain should be used. See pages 227 and 242.