



FASTENERS

316 STAINLESS LACING WITH 300 SERIES STAINLESS CORRUGATED HINGE PINS

BELT WIDTH		ORDERING NUMBER	ITEM CODE	WT. KGS.	ORDERING NUMBER	ITEM CODE	WT. KGS.	ORDERING NUMBER	ITEM CODE	WT. KGS.	ORDERING NUMBER	ITEM CODE	WT. KGS.	ORDERING NUMBER	ITEM CODE	WT. KGS.
mm	in.	00S			1S			1BS			7S			15S		
300	12"	00S-12	10528	0.1	1S-12	10545	0.2	Note: Size 1S and 1BS Alligator lacing has been modified to allow for complete interchangeability. For machine applied lacing, order the corresponding 1S size.			7S-12	10562	0.3	15S-12	10491	0.5
350	14"	00S-14	10529	0.2	1S-14	10546	0.2				7S-14	10563	0.4	15S-14	10579	0.5
400	16"	00S-16	10530	0.2	1S-16	10547	0.4				7S-16	10564	0.5	15S-16	10580	0.6
450	18"	00S-18	10531	0.2	1S-18	10548	0.4				7S-18	10565	0.5	15S-18	10581	0.7
500	20"	00S-20	10532	0.3	1S-20	10549	0.5				7S-20	10566	0.5	15S-20	10582	0.8
600	24"	00S-24	10534	0.3	1S-24	10551	0.5				7S-24	10568	0.6	15S-24	10584	0.9
700	28"										7S-28	10570	0.7	15S-28	10586	1.0
750	30"	00S-30	10537	0.4	1S-30	10554	0.6				7S-30	10571	0.8	15S-30	10587	1.1
900	36"	00S-36	10539	0.5	1S-36	10556	0.8				7S-36	10573	1.0	15S-36	10589	1.3
1050	42"	00S-42	10540	0.5	1S-42	10557	0.9				7S-42	10574	1.1	15S-42	10590	1.6
1200	48"	00S-48	10541	0.6	1S-48	10558	1.0				7S-48	10575	1.2	15S-48	10591	1.8
1350	54"				1S-54	10559	1.4									
1500	60"	00S-60	10543	0.8	1S-60	10560	1.3				7S-60	10577	1.7	15S-60	10593	2.2
		00S-600	13394	0.3	1S-600	13873	0.5				7S-600	13892	0.7			
		00S-900	13844	0.5												
		20S			25S			27S			35S			45S		
300	12"	20S-12	10492	0.6	25S-12	10493	0.7	27S-12	10494	0.8	35S-12	10495	1.3	45S-12	10496	1.5
350	14"	20S-14	10595	0.7	25S-14	10611	0.8	27S-14	10627	1.0	35S-14	10643	1.5			
400	16"	20S-16	10596	0.8	25S-16	10612	0.9	27S-16	10628	1.1	35S-16	10644	1.8			
450	18"	20S-18	10597	0.9	25S-18	10613	1.0	27S-18	10629	1.2	35S-18	10645	1.9	45S-18	10661	2.4
500	20"	20S-20	10598	1.0	25S-20	10614	1.1	27S-20	10630	1.4	35S-20	10646	2.1			
600	24"	20S-24	10600	1.2	25S-24	10616	1.4	27S-24	10632	1.4	35S-24	10648	2.5	45S-24	10664	3.2
750	30"	20S-30	10603	1.5	25S-30	10619	1.7	27S-30	10635	2.0	35S-30	10651	3.2	45S-30	10667	3.7
900	36"	20S-36	10605	1.8	25S-36	10621	2.0	27S-36	10637	2.4	35S-36	10653	3.8	45S-36	10669	4.7
1050	42"	20S-42	10606	2.1	25S-42	10622	2.2	27S-42	10638	2.8	35S-42	10654	4.6	45S-42	10670	5.4
1200	48"	20S-48	10607	2.4	25S-48	10623	2.6	27S-48	10639	3.2	35S-48	10655	5.0	45S-48	10671	6.3
1500	60"	20S-60	10609	3.0	25S-60	10625	3.4	27S-60	10641	3.9	35S-60	10657	6.4			
		55S														
450	18"	55S-18	10677	3.3												
600	24"	55S-24	10680	4.4												
750	30"	55S-30	10683	5.4												
900	36"	55S-36	10685	7.6												
1200	48"	55S-48	10687	8.7												

 **Stock Items** (non-shaded) carried in factory inventory.

 **Made To Order Items** (shaded) allow one week for production. In most cases, the next standard stock item can be adapted to meet your requirements.

Non-Listed Items are available. Request quote for price and delivery.