

Alligator® Ready Set™ Staple Fasteners



FASTENERS

CARTON CONTENTS:

- 4 Fastener Sets
- 4 Hinge Pins
- Required Amount of Retaining Washers

STEEL

RS62	BELT WIDTH		ORDERING NUMBER	ITEM CODE	WT. KGS.
	mm	in.	WITH NYLON COVERED STEEL CABLE PINS (NC)		
	300	12"	RS62J12/300NC	54476	0.6
	400	16"	RS62J16/400NC	54477	0.8
	450	18"	RS62J18/450NC	54478	0.9
	500	20"	RS62J20/500NC	54479	1.0
	600	24"	RS62J24/600NC	54480	1.2
	750	30"	RS62J30/750NC	54481	1.5
	900	36"	RS62J36/900NC	54482	1.8
	1000	40"	RS62J40/1000NC	54646	2.1
	1050	42"	RS62J42NC	54485	2.1
	1200	47"	RS62J47/1200NC	54647	2.4
	1200	48"	RS62J48NC	54483	2.4
	1500	60"	RS62J60NC	54484	3.0

STAINLESS (TYPE 316)

RS62	BELT WIDTH		ORDERING NUMBER	ITEM CODE	WT. KGS.
	mm	in.	WITH NYLON COVERED STAINLESS CABLE PINS (NCS)		
	300	12"	RS62SJ12/300SS	54494	0.6
	400	16"	RS62SJ16/400SS	54495	0.8
	450	18"	RS62SJ18/450SS	54496	0.9
	500	20"	RS62SJ20/500SS	54497	1.0
	600	24"	RS62SJ24/600SS	54498	1.2
	750	30"	RS62SJ30/750SS	54499	1.5
	900	36"	RS62SJ36/900SS	54500	1.8
	1000	40"	RS62SJ40/1000SS	54501	2.1
	1050	42"	RS62SJ42SS	54503	2.1
	1200	47"	RS62SJ47/1200SS	54504	2.4
	1200	48"	RS62SJ48SS	54505	2.4
	1500	60"	RS62SJ60SS	54506	3.0

STEEL

RS125	BELT WIDTH		ORDERING NUMBER	ITEM CODE	WT. KGS.
	mm	in.	WITH NYLON COVERED STEEL CABLE PINS (NC)		
	100	4"	RS125J4NC*	54513	0.7
	250	10"	RS125J10NC	54514	0.8
	300	12"	RS125J12/300NC	54515	0.9
	350	14"	RS125J14NC	54516	1.0
	400	16"	RS125J16/400NC	54517	1.1
	450	18"	RS125J18/450NC	54518	1.3
	500	20"	RS125J20/500NC	54519	1.5
	600	24"	RS125J24/600NC	54520	1.7
	750	30"	RS125J30/750NC	54521	2.0
	900	36"	RS125J36/900NC	54522	2.5
	1000	40"	RS125J40/1000NC	54670	2.9
	1050	42"	RS125J42NC	54523	3.0
	1200	47"	RS125J47/1200NC	54671	3.3
	1200	48"	RS125J48NC	54524	3.4
	1500	60"	RS125J60NC	54525	4.2

STAINLESS (TYPE 316)

RS125	BELT WIDTH		ORDERING NUMBER	ITEM CODE	WT. KGS.
	mm	in.	WITH NYLON COVERED STAINLESS CABLE PINS (NCS)		
	100	4"	RS125SJ10NCS	54549	0.7
	250	10"	RS125SJ10/300NCS	54550	0.9
	300	12"	RS125SJ12/300SS	54537	0.9
	350	14"	RS125SJ14SS	54538	1.1
	400	16"	RS125SJ16/400SS	54539	1.3
	450	18"	RS125SJ18/450SS	54540	1.4
	500	20"	RS125SJ20/500SS	54541	1.6
	600	24"	RS125SJ24/600SS	54542	1.8
	750	30"	RS125SJ30/750SS	54543	2.2
	900	36"	RS125SJ36/900SS	54544	2.7
	1000	40"	RS125SJ40/1000SS	54545	3.2
	1050	42"	RS125SJ42SS	54547	3.2
	1200	47"	RS125SJ47/1200SS	54548	3.6
	1200	48"	RS125SJ48SS	54549	3.6
	1500	60"	RS125SJ60SS	54550	4.6

*10 Sets per Box

BULK PACKS

ORDERING NUMBER	ITEM CODE	WT. KGS.
RS125S-600 (25 sets)	54464	12.3
RS125S-900 (55 sets)	55478	34.5

STEEL

RS187	BELT WIDTH		ORDERING NUMBER	ITEM CODE	WT. KGS.
	mm	in.	WITH NYLON COVERED STEEL CABLE PINS (NC)		
	100	4"	RS187J4NC*	54587	1.0
	300	12"	RS187J12/300NC	54588	1.2
	400	16"	RS187J16/400NC	54589	1.7
	450	18"	RS187J18/450NC	54590	1.9
	500	20"	RS187J20/500NC	54591	2.2
	600	24"	RS187J24/600NC	54592	2.5
	750	30"	RS187J30/750NC	54593	3.1
	900	36"	RS187J36/900NC	54594	3.7
	1050	42"	RS187J42NC	54595	4.3
	1200	47"	RS187J47/1200NC	54596	4.5
	1200	48"	RS187J48NC	54597	4.5
	1500	60"	RS187J60NC	54597	5.4

STAINLESS (TYPE 316)

RS187	BELT WIDTH		ORDERING NUMBER	ITEM CODE	WT. KGS.
	mm	in.	WITH NYLON COVERED STAINLESS CABLE PINS (NCS)		
	100	4"	RS187SJ12/300SS	54765	1.5
	300	12"	RS187SJ16/400SS	54613	1.8
	400	16"	RS187SJ18/450SS	54606	2.0
	450	18"	RS187SJ20/500SS	54624	2.3
	500	20"	RS187SJ24/600SS	54607	2.7
	600	24"	RS187SJ30/750SS	54608	3.4
	750	30"	RS187SJ36/900SS	54609	4.0
	900	36"	RS187SJ42SS	54610	4.4
	1050	42"	RS187SJ47/1200SS	54611	5.4
	1200	47"	RS187SJ48SS	54612	5.4
	1200	48"	RS187SJ60SS	54612	6.3

*10 Sets per Box

PLEASE NOTE: 310 Alligator Staple is no longer available.

MAGNETIC STAINLESS (TYPE 430)

ORDERING NUMBER	ITEM CODE	WT. KGS.
RS62MJ24/600MS	54473	1.2
RS125MJ24/600MS	54566	1.7

STAPLE LENGTHS

RS62 = 9.4 mm (.37")
RS125 = 11.4 mm (.45")
RS187 = 13.2 mm (.52")

NOTE: Plate, Staples, and Hinge Pins are all Magnetic Stainless Steel.

www.flexco.com • Customer Service: 1300-098-435

