



CEHS-SN 01

CEHS-SN 01 cable

The CEHS-SN 01 cable for electronic hook switch is ideal for all users of professional wireless headsets, in combination with one of following EHS-compatible SNOM phones:

- Snom 320
- Snom 360
- Snom 370
- Snom 820

This new cable is an enhancement for any contact center or corporate office environment. It has been specially designed to make calls convenient to manage – thanks to easy set-up, single-button operation as well as efficient and flexible answering/ending of calls. The CEHS-SN 01 is compatible with the wireless office headsets by Sennheiser Communications – DW Office, DW Pro 1, DW Pro 2 and D 10.

Benefits and Features:

- Remotely answer your phone calls
- Handle all calls by the press of a single button, i.e. end the call
- Get notified from the distance about incoming calls by the ring tone in the headset
- Efficient and flexible call handling i.e. take or end the call
- Call control towards the phone without using a mechanical handset lifter
- Easy setup

Product Information

CEHS-SN 01

EAN No.	40 44155 04739 4
UPC No.	6 15104 17408 5
Art. No.	504101
General Data	
Cable length	100 cm / 39.4 in
Cable weight	40 g / 1.35 oz
Connector	RJ 45
Compatible with	DW Office, DW Pro 1, DW Pro 2 and D 10
Minimum order quantity	10 units
Compatible SNOM phones	Snom 320 Snom 360 Snom 370 Snom 820

Packaging	
Dimensions of product packaging	225 x 150 x 25 mm / 8.4 x 5.9 x 1.0 in (L x W x H)
Weight unit	60 g / 2.03 oz
Units in distributor carton	10
Dimensions of distributor carton	155 x 203 x 160 mm / 6.11 x 8 x 6.30 in (L x W x H)
Distributor PE bag in weight incl. products	693 g / 23.43 oz
Units in master carton	80
Dimensions of master carton	330 x 430 x 360 mm / 13 x 16.93 x 14.18 in (L x W x H)
Master carton weight incl. products	5.8 kg / 196.12 oz
Content of delivery	SNOM EHS cable, quick guide
Warranty	2 years