




PART NUMBER	CIRCULAR MIL RANGE		A ± .03	I.D. ± .03	O.D. REF.
	MIN.	MAX.			
PS8-L	19,000	25,000	.40	.22	.31
PS6-L	25,000	40,000	.44	.28	.38
PS4-L	40,000	65,000	.54	.31	.42
PS2-Q	65,000	100,000	.64	.39	.52
PS1-E	100,000	130,000	.67	.45	.58
PS1/0-X	130,000	160,000	.73	.51	.64
PS2/0-X	160,000	200,000	.72	.57	.71
PS3/0-X	200,000	240,000	.75	.63	.77
PS4/0-X	240,000	280,000	.77	.65	.81

NOTES:

- PART NUMBER AND PANDUIT TO BE METAL MARKED IN EACH PART.
- PACKAGE QTY. -X=10
-E=20
-Q=25
-L=50

A41041_05

05	2/05	JHNU		ADDED CIRCULAR MIL RANGE TO TABLE.				 PANDUIT CORP. TINLEY PARK, ILLINOIS PARALLEL SPLICES #8 THRU 4/0 AWG (COPPER)
04	1/01	EJS	RLS	ADDED PACKAGE CODE TO PART NUMBER, ADDED NOTE 2, DRAWING VOID, REFER TO DWG C41302		DBH	LA	
03	5/98	TM	RLS	ADDED O.D. AND UPDATED DIMS	06811	DBH	LA	
02	10/94	MS	RS	UPDATED AND REDRAWN ON CAD	02513	LA	TKE	
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	DRAWN BY MS CHK'D RS SCALE NONE DRAWING NO. A41041