

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NUMBER	DESCRIPTION	WEIGHT
BKA6ASD8INBL	CATEGORY 6A BREAK-AWAY ADAPTER	.44 lb/10 PCS [198 g/10 PCS]

NOTES:

1. NOMINAL JACKET DIAMETER IS .240in. (6.096mm).
2. CONSTRUCTED WITH 26AWG STRANDED CAT 6A UTP CM RATED CABLE.
3. TERMINATED WITH (8 POSITION) CAT 6A MODULAR PLUG AT ONE END PER T568B AND CAT6A MODULAR JACK WITH BREAK-AWAY RELEASE FEATURE ON OTHER END.
4. 100% FACTORY TESTED TO CATEGORY 6A PATCH CORD COMPONENT LIMITS.
5. MATERIALS:
PLUG: POLYCARBONATE
BOOTS: TPV
JACK HOUSING: ABS
6. DIMENSIONS IN [] ARE IN METRIC.

T568B WIRING SCHEME

PLUG POSITION:	CABLE WIRE:
1	WHITE/ORANGE
2	ORANGE
3	WHITE/GREEN
4	BLUE
5	WHITE/BLUE
6	GREEN
7	WHITE/BROWN
8	BROWN



PART NUMBER		BKA6ASD8INBL	
TITLE		BREAK-AWAY ADAPTER	
CUSTOMER DRAWING			
ITEM REVISION NAME		14M532AD/00	
DATASET FILE NAME		14M532AD_DC02/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL: SEE NOTE 5	
DRAWING NUMBER: 14M532AD-02			
DRAWN BY BJN	DATE 10-7-15	CHK JAV	SCALE NONE
SHT 1 OF 1		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	4-8-16	BJN	JAV	TMBA	UPDATED	14M532AD-02
R	11-30-15	BJN	JAV	TMBA	RELEASED TO PRODUCTION	14M532AD-02