





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT*
SEE TABLE 1	.45 LB/100 PCS (203 g/100 PCS)

* WEIGHT IS APPROXIMATE


NOTES:

1. MINI-COM TG 45° LEFT-RIGHT WIRE CAP
2. TERMINATES ALL CJ**TG** UTP JACK MODULES.
3. WIRE CAP TERMINATES CABLE TO THE RIGHT OR TO THE LEFT.
4. TERMINATES 22-26 AWG SOLID OR STRANDED UTP CABLE.
5. MATERIAL: POLYCARBONATE
6. DIMENSIONS IN BRACKETS ARE METRIC.

TABLE 1 - PART NUMBERS

PART NUMBER	COLOR	PERFORMANCE CATEGORY
CJLRCAPBU-%	BLUE	CATEGORY 6A
CJLRCAPIW-%	INTERNATIONAL WHITE	CATEGORY 6
CJLRCAPRD-%	RED	CATEGORY 5E

PRODUCT SPEC	N/A	PACKAGING SPEC	N/A
PART NUMBER	SEE TABLE 1	WORK INSTRUCTION	N/A
INSPECTION INSTRUCTION NUMBER	N/A	FMEA & CONTROL PLAN NUMBER	N/A

TITLE				MINI-COM TG 45° LEFT-RIGHT WIRE CAP			
				CUSTOMER DRAWING			
ITEM REVISION NAME							
00153LAF/00							
DATASET FILE NAME							
00153LAF_DC02/00B							
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION				MATERIAL:			
				SEE NOTE 5			
				DRAWING NUMBER:			
				00153LAF - 02			
DRAWN BY		DATE		CHK		SCALE	
BJN		10-14-16		JAV		NNOE	
						SHT 1 OF 1	
						A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	1-16-17	BJN	JAV	TMBA	UPDATED	00153LAF-02
1	10-27-16	BJN	JAV	TMBA	RELEASED TO PRODUCTION	00153LAF-02
R	10-14-16	BJN	JAV		DRAWING RELEASED	