

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
F		T	Y			E	L	2						

FIBER TYPE

- 9 - OS1/OS2
- X - OM3
- Z - OM4

FLAME RATING

- L - LSZH
- P - OFNP

CONNECTOR TYPE

- 5 - MTP (FEMALE)
- 6 - MTP (MALE)
- 7 - PANMPO (FEMALE)
- 8 - PANMPO (MALE)

PERFORMANCE/POLARITY

- S - STANDARD PERFORMANCE (SEE NOTE 8)
- O - OPTIMIZED PERFORMANCE (SEE NOTE 8)

PULLING EYE

- A - PULLING EYE (MTP/PANMPO END)
- N - NO PULLING EYE

UNIT OF MEASURE

- M - METERS
- F - FEET

LENGTH

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00	09-18-13	SAT	WMA		RELEASED TO PRODUCTION	12F178BN-DC

TITLE 12 FIBER MPO TO LC SMALL DIAMETER TRUNK CABLE WITH PULLING EYE CUSTOMER DRAWING	
ITEM REVISION NAME 12F178BN/00	PANDUIT
DATASET FILE NAME 12F178BN_DC/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
.X ± .03 [0.8]	.XXX ± .010 [0.3]
.XX ± .03 [0.8]	ANGLES ±
THIRD ANGLE PROJECTION	
DRAWING NUMBER: 12F178BN-DC	
DRAWN BY SAT	DATE 09-18-13
CHK WMA	SCALE NONE
SHT 2 OF 2	
SIZE B	

2

1

2

1

B

A