



CT-2980/ST • CT-2980/STINT • CT-2980/STUK
• CT-2980/STAUS • CT-2980/TO
DIE-LESS CRIMP TOOL

This tool meets requirements of Safety for Hand Heldheld, Motor-Operated Electric Tools specification UL 60745-1 and CSA C22.2 No 60745-1. Tool is listed under CSA file number 268531.

NOTES, UNLESS OTHERWISE SPECIFIED:

The CT-2980/ST, CT-2980/STINT, CT-2980/STUK, CT-2980/STAUS and CT-2980/TO Battery Operated Die-less Crimping Tools are designed to crimp:

- Crimps Panduit Copper and Aluminum compression connectors. Go to www.panduit.com for more information.

The CT-2980/ST, CT-2980/STINT, CT-2980/STUK and CT-2980/STAUS Tools include:

Qty.	Description / Item			
1	Battery Operated Hydraulic Die-Less Crimp Tool			
2	Rechargeable Battery (Makita Lithium-Ion 18VDC, 3Ah)			
1	Makita Battery Charger – Regional (reference images below for regional plug type)			
	/ST	/STINT	/STUK	/STAUS
	Plug Type A (North America)	Plug Type C (International)	Plug Type G (UK)	Plug Type I (Australia)
1	Plastic Tool Case			
1	Tool Carrying Strap			

The CT-2980/TO Tool includes:

Qty.	Description / Item
1	Battery Operated Hydraulic Die-Less Crimp Tool

Technical Information:

Tool Weight (including battery)	10.8 lbs. (4.9 kg)
Dimensions (including battery)	15.7" L x 13.5" H x 3.0" W [400 L x 344 H x 75 W] mm
Crimping Force	6.2 tons (55 kN)

A copy of the operation manual and accessory information can be found at: www.panduit.com.

Dimensions in [brackets] are in millimeters. All dimensions are for reference only.

CT-2980/ST, CT-2980/STINT,
CT-2980/STUK, CT-2980/STAUS
and CT-2980/TO
CUSTOMER DRAWING


ITEM REVISION NAME:

00084SLE_DC/00

PANDUIT

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.x) ± --- (.xxx) ± ---
(.xx) ± --- ANGLES ± ---



THIRD ANGLE
PROJECTION

MATERIAL:

DRAWING NUMBER:
00084SLE_DC

DRAWN BY:
BLR

DATE:
7-21-16

CHK
BJPU

SCALE
NONE

SHT 1 OF 1

SIZE
B

00	7-25-16	BAK	ACC	JADE	DRAWING RELEASED	010819
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN