

2



1




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
GM-A0262**	6.17kg (13.6lb)

NOTES:  
1. IDENTIFICATION: VERTICAL, MIXED (18) LOCKING C13 & (6) LOCKING C19, GATEWAY-ENABLE MONITORED, 230V / 16A / SINGLE-PHASE PDU


PART NO.	COLOR
GM-A0262**	BLACK

2. ACCESSORY COMPONENTS:  
(1) QUICK-START GUIDE
3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
4. INPUT POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. WHEN CONNECTED VIA SERIAL CONNECTION TO GATEWAY, DATA CAN BE ACCESSED VIA ON UNIT DISPLAY OR REMOTELY.
5. RoHS COMPLIANT.
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
7. MAXIMUM AVAILABLE INPUT POWER = 3.6 kW
8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.
9. PRINTED WITH CURCUIT IDENTIFICATION




FRONT VIEW


SIDE VIEW



PLUG  
16 AMP 250V  
2P/3W  
IEC 60309, SPLASHPROOF



EIGHTEEN (18)  
LOCKING RECEPTACLES  
10 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C13



SIX (6)  
LOCKING RECEPTACLES  
16 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C19

01B	1-4-16	MRWA	GLM	EDM	A. DRAWING WAS INCORRECTLY LABELED "CONTROL "	AA0262AP
01A	03/10/15	PJST	GLM	EDM	REVISED DISPLAY ORIENTATION	AA0262AP
00A	10-23-14	GLM	GLM	EDM	RELEASED TO PRODUCTION	AA0262AP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE			
SMARTZONE GATEWAY-ENABLED M SERIES RACK PDU			
GM-A0262**			
CUSTOMER DRAWING			
ITEM REVISION NAME			
AA0262AP/01.PRT			
DATASET FILE NAME		MATERIAL/COLOR:	
AA0262CP_DC/01B.PRT		N/A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		DRAWING NUMBER:	
INCHES +/- 0.03 METRIC - MILLIMETER +/- 0.8		AA0262AP_DC	
X.X +/- 0.018 X.X +/- 0.46			
X.XX +/- 0.007 X.XX +/- 0.18			
		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
GLM	10-23-14	GLM	NONE
SHT 1 OF 1		SIZE	
		B	