

2





1



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
Q1L2B2P6M24AQA0	X.XXkg (X.XXlb)



- NOTES:
- IDENTIFICATION: VERTICAL, MIXED (12) C13 LOCKING, (12) C19 LOCKING, NETWORK-ENABLED MONITORED WITH MONITORED AND SWITCHED PER OUTLET, 230/400V / 32A / THREE-PHASE WYE PDU



- PART NO. COLOR
Q1L2B2P6M24AQA0 BLACK
- ACCESSORY COMPONENTS:
(1) QUICK-START GUIDE
 - PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
 - PHASE (L1, L2, L3) LEVEL POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. DATA CAN BE ACCESSED ON UNIT DISPLAY OR REMOTELY WHEN CONNECTED VIA ETHERNET CONNECTION.
 - OUTLET LEVEL POWER (AMPS, VOLTS, POWER FACTOR, FREQUENCY) MONITORING CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION
 - INDIVIDUAL RECEPTACLES CAN BE SWITCHED ON/OFF REMOTELY
 - RoHS COMPLIANT
 - VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
 - MAXIMUM AVAILABLE INPUT POWER = 22.2 kW
 - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
 - PRINTED WITH PHASE & CIRCUIT IDENTIFICATION



03A	2-4-15	MRWA	GLM	EDM	RELEASED TO PRODUCTION	12V091Q0
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN									
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE									
		PRINT									
TITLE											
SMARTZONE NETWORK-ENABLED MSPQ SERIES RACK PDU											
Q1L2B2P6M24AQA0											
CUSTOMER DRAWING											
ITEM REVISION NAME											
12V091Q0/03.PRT											
DATASET FILE NAME		MATERIAL/COLOR:									
12V091Q0_DC/03A.PRT											
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		N/A									
<table><tr><td>INCHES</td><td>METRIC - MILLIMETER</td><td>ANGLE</td></tr><tr><td>X.X +/-</td><td>X +/-</td><td rowspan="3">+/-</td></tr><tr><td>X.XX +/-</td><td>X.X +/-</td></tr><tr><td>X.XXX +/-</td><td>X.XX +/-</td></tr></table>				INCHES	METRIC - MILLIMETER	ANGLE	X.X +/-	X +/-	+/-	X.XX +/-	X.X +/-
INCHES	METRIC - MILLIMETER	ANGLE									
X.X +/-	X +/-	+/-									
X.XX +/-	X.X +/-										
X.XXX +/-	X.XX +/-										
		DRAWING NUMBER:									
THIRD ANGLE PROJECTION		12V091Q0_DC									
DRAWN BY	DATE	CHK	SCALE								
MRWA	2-4-15	GLM	NONE								
SHT 1 OF 1			SIZE								
			B								