


PART #	COLOR	A (REF) IN (mm)	B (REF) IN (mm)	C IN (mm)	APPROXIMATE WEIGHT LBS. (g)
PC20C19BL3	BLACK	0.37 (9.4)	2.09 (53)	36 (914)	.48 (216)
PC20C19BL4				48 (1219)	.59 (267)
PC20C19BL5				60 (1524)	.70 (317)
PC20C19BL6				72 (1830)	.81 (367)
PC20C19BL8				96 (2138)	1.03 (467)
PC20C19GY3	GRAY			36 (914)	.48 (216)
PC20C19GY4				48 (1219)	.59 (267)
PC20C19GY5				60 (1524)	.70 (317)
PC20C19GY6				72 (1830)	.81 (367)
PC20C19GY8				96 (2138)	1.03 (467)



NOTES:

1. SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. RATING: 15A/250V AC.
3. CORD ASSEMBLY HAS THESE APPROVALS: VDE, CE, UL, CSA OR cUL.
4. PRODUCT IS RoHS COMPLIANT.

											PANDUIT CORP TINLEY PARK, ILLINOIS CUSTOMER DRAWING IEC60320-C20 TO IEC60320-C19 POWER CORD							
											UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1 (.XXX) ± .005 (.XX) ± .01 ANGLES ± 5°			UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION				
OOB	8/8/12	DBLA	DJW	ADDITION OF 8' CORDS				GAECN00170	OO	KLN		DRAWN BY RVU		MAT'L: SEE NOTES		SCALE 1 : 1		
OOA	7/19/12	DBLA	DJW	INITIAL DRAWING RELEASE				GAECN00096	OO	KLN		DATE 5/22/12				DRAWING NO.		DWG
REV	DATE	BY	CHK	DESCRIPTION				ECN	-	R	CUST	SUP	OC			CHK'D KLN	11K026B1-DC	
																	SIZE	