


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
R4P79	96 LBS/EACH 43.6 kg/EACH
R4PCN79	88 LBS/EACH 40.0 kg/EACH
R4P79GY/N	96 LBS/EACH 43.6 kg/EACH



NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- DIMENSIONS IN PARENTHESIS ARE METRIC.
- INDEPENDENT ADJUSTABLE FRONT & REAR MOUNTING RAILS (EIA) ADJUST FROM 2.75" TO 30" DEPTH.
- CAN BE USED WITH ANY EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
- 42 AVAILABLE RACK SPACES.
- EIA UNIVERSAL STANDARD HOLE PROGRESSION ON FRONT CHANNELS AND REAR MOUNT RAILS .625", .625", .500", .625", .625", .500"...ETC.
- ALL RACKS WILL HAVE NUMBERS UP ORIENTATION (RU "01" ON BOTTOM, RU "42" ON TOP). INSTRUCTIONS WILL BE PROVIDED ON HOW TO GET NUMBERS DOWN ORIENTATION.
- RU SPACING NUMBERS ARE CLEARLY PRINTED ON MOUNTING RAILS.
- ALL ASSEMBLY HARDWARE INCLUDED:
 - (16) 3/8-16 X 1" BLACK HEX BOLT
 - (16) 3/8" PAINT PIERCING GROUNDING WASHER
 - (1) TUBE OF ANTI-OXIDIZING PASTE
 - (25) 12-24 X .5" SLOTTED PAN HEAD STEEL SCREW
 - (25) #12-24 CAGE NUTS (ONLY PROVIDED FOR R4PCN)
- EASY ASSEMBLY, ONE WRENCH NEEDED TO INSTALL BOLTS INTO WELDNUTS IN ALL 8 CORNERS.
- FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
- LOAD RATING - 2500 LBS.





TITLE		30" DEEP 4 POST RACK (R4P79, R4PCN79, R4P79GY/N)	
ITEM REVISION NAME		CUSTOMER DRAWING	
V10687AP/06		PANDUIT	
DATASET FILE NAME		V10687AP_DC/06A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XX ±		STEEL	
.XXX ± ANGLES ±		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		V10687AP-DC	
DRAWN BY	DATE	CHK	SCALE
PM	7-27-10	DPN	NONE
SHT 1 OF 3			SIZE
			A

06A	7-17-16	BAME	RYB	KRKE	UPDATED FEATURE ON PAGE 3 AND DIMS ON PAGE 2	M09000EF
05A	3-28-13	PM	BJA	CMK	B. ADDED R4P79GY/N INFORMATION A. REPLACED DRAWING BORDER	V10679AP-DC
04A	9-13-11	PM	SRK	CMK	REVISED COMPONENT GEOMETRY	V10679AP-DC
03A	9-7-10	PM	DPN	CMK	RELEASED TO PRODUCTION	V10679AP-DC
02A	7-27-10	PM	DPN	CMK	DRAWING RELEASED	V10679AP-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

2




1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FLOOR FOOTPRINT WITH
BASE ANGLES TURNED
OUTWARD FOR EXTENDED
FOOTPRINT

FLOOR FOOTPRINT WITH
BASE ANGLES TURNED INWARD

TITLE		 30" DEEP 4 POST RACK (R4P79, R4PCN79, R4P79GY/N)	
ITEM REVISION NAME		CUSTOMER DRAWING	
V10687AP/06			
DATASET FILE NAME			
V10687AP_DC/06A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .XX ± ANGLES ±			
 THIRD ANGLE PROJECTION		MATERIAL: STEEL	
DRAWN BY		DRAWING NUMBER:	
PM		V10687AP-DC	
DATE		SHT 2 OF 3	
7-27-10		A	
CHK		SIZE	
DPN		A	
SCALE			
NONE			

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
06A	7-27-16	BAME	RYB	KRKE	SEE SHEET 1 OF 3 FOR REVISIONS	M09000EF
05A	3-28-13	PM	BJA	CMK	SEE SHEET 1 OF 3 FOR REVISIONS	V10679AP-DC
04A	9-13-11	PM	SRK	CMK	SEE SHEET 1 OF 3 FOR REVISIONS	V10679AP-DC
03A	9-7-10	PM	DPN	CMK	SEE SHEET 1 OF 3 FOR REVISIONS	V10679AP-DC
02A	7-27-10	PM	DPN	CMK	SEE SHEET 1 OF 3 FOR REVISIONS	V10679AP-DC

2

1

B

A

A

A

D10100DA/15

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

J-HOOKS UP TO 3/8" DIA.
MAY BE MOUNTED FROM
THE FRONT OF THE BASE
ANGLES

BONUS HOLES ARE FOR
MOUNTING PANDUIT
ACCESSORIES. SEE
NOTE 1.

MOUNTING HOLES FOR
OPTIONAL POWER STRIP
BRACKET. BRACKETS CAN
BE MOUNTED ON ANY
OF THE 4 POSTS OR
ADJUSTABLE RAILS.

OPTIONAL POST HOLES
FOR BRACKET MOUNTING
NETRUNNER

MASKED AREA
FOR GROUNDING,
TOP & BOTTOM
OF RACK.
4 PLACES

BASE ANGLES
(SEE SHEET 2 FOR
MOUNTING POSITIONS)

"J" BOLT MOUNTING HOLES FOR
SECURING LADDER RACK
PERPENDICULAR AND PARALLEL
TO 4 POST RACK.

MOUNTING RAILS
(ADJUSTABLE FROM
2.75" TO 30")

CUTOUTS ARE FOR MOUNTING
PANDUIT ACCESSORIES
SEE NOTE 1.

CROSS BEAMS ARE MARKED
EVERY 1/2" FOR MOUNTING
RAIL ALIGNMENT

MOUNTING HOLES FOR
VERTICAL MANAGERS.
DOUBLE HOLES ARE FOR
MOUNTING PATCHRUNNER.
SINGLE HOLES ARE FOR
SIDE MOUNTING NETRUNNER.

RU SPACINGS ARE
PRINTED ON
MOUNTING RAILS

R4P79 AND R4P79GY/N
RAILS HAVE
TAPPED HOLES

R4P79CN RAILS HAVE
CAGE NUT HOLES

06A	7-27-16	BAME	RYB	KRKE	SEE SHEET 1 OF 3 FOR REVISIONS	M09000EF
05A	3-28-13	PM	BAK	CMK	SEE SHEET 1 OF 3 FOR REVISIONS	V10679AP-DC
04A	9-13-11	PM	SRK	CMK	SEE SHEET 1 OF 3 FOR REVISIONS	V10679AP-DC
03A	9-7-10	PM	DPN	CMK	SEE SHEET 1 OF 3 FOR REVISIONS	V10679AP-DC
02A	7-27-10	PM	DPN	CMK	SEE SHEET 1 OF 3 FOR REVISIONS	V10679AP-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE		30" DEEP 4 POST RACK (R4P79, R4PCN79, R4P79GY/N)	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		V10687AP-DC	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ±		STEEL	
.XX ±		DRAWING NUMBER:	
.XXX ±		V10687AP-DC	
ANGLES ±		SHT 3 OF 3	
THIRD ANGLE PROJECTION		SIZE	
DRAWN BY		A	
DATE		7-27-10	
CHK		DPN	
SCALE		NONE	