

CTM010M4



Article Number: 151-30305

Cable Tie Mount, 0.15" Hole Dia., 0.2" Max Tie Width, PA66, White, 1000/pkg

 **RoHS**

Base Data

Local Order Number	CTM010M4
Type	CTM0
Color	White (WH)
Features and Benefits	• Designed for use with 18 through 50 pound cable ties to provide stability when securing bundles. • Secures with a single screw providing quick installation.
Product Description	HellermannTyton cable tie mounts are designed for use with 18 through 120 pound cable ties to provide stability when securing bundles. The mounts are installed quick and easy by securing a single screw.
Fixation Method (FF)	Screw Mounting and Rivet
Short Description	Cable Tie Mount, 0.15" Hole Dia., 0.2" Max Tie Width, PA66, White, 1000/pkg

Product Dimensions

Length L (imperial)	0.58 "
Length L (metric)	14.7 mm
Width W (imperial)	0.37 "
Width W (metric)	9.4 mm
Cable Tie Width Max (imperial)	0.2 "
Cable Tie Width max. (metric)	5.0 mm
Height H (imperial)	0.27 "
Height H (metric)	6.9 mm
Mounting Hole Diameter D (imperial)	0.15 "
Mounting Hole Diameter D (metric)	3.8 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	1000
Carton Quantity	15000

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
CSA Certified	No
Flammability	UL94 V2
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	Yes
Certification / Specification	UL

UL Listed (US and Canada) No

UL Recognized (US and Canada) Yes