

T18MR9M4



Article Number: 113-00028

Screw Mount Tie, 18lb 4.3" Long, Max Bun Diameter .79", #4 Screw, PA66, Natural, 100/pkg

 RoHS

Base Data

Local Order Number	T18MR9M4
Type	T18MR
Color	Natural (NA)
Features and Benefits	• Mount design secures firmly on any #4 Screw • Screw mount style creates low insertion and high extraction force.
Product Description	Screw Mount Cable Ties are made of all plastic and provide a quick and simple method of mounting.
Fixation Method (FF)	fixing hole
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Short Description	Screw Mount Tie, 18lb 4.3" Long, Max Bun Diameter .79", #4 Screw, PA66, Natural, 100/pkg

Product Dimensions

Minimum Tensile Strength (imperial)	18.0 lbs
Minimum Tensile Strength (N)	80 N
Length L (imperial)	4.3 "
Length L (metric)	110.0 mm
Width W (imperial)	0.1 "
Width W (metric)	2.5 mm
Height H (imperial)	0.17 "
Height H (metric)	4.2 mm
Bundle Diameter min (imperial)	0.06 "
Bundle Diameter min (metric)	1.5 mm
Bundle Diameter max (imperial)	0.8 "
Bundle Diameter max (metric)	20.0 mm
Mounting Hole Diameter D (imperial)	0.12 "
Mounting Hole Diameter D (metric)	3.1 mm
Thickness T (imperial)	0.039 "
Thickness T (Metric)	1.0 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	1000

Carton Quantity 10000

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
CSA Certified	No
Flammability	UL94 V2
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	Yes
Certification / Specification	UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes