

156-00592



Article Number: 156-00592

Cable Tie and Edge Clip, 50lb, 8.0" Long, EC23, Panel Thickness .12"-.24", PA66UV, Black, 100/bag



## Base Data

Local Order Number 156-00592

Type T50REC23

Color Black (BK)

- Features and Benefits**
- Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.
  - Edge Clip provides low insertion force and high extraction force ideal for assembly environments.
  - Two piece assembly allows the mount to slide along the strap ensuring proper orientation.

**Product Description** The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

**Fixation Method (FF)** EdgeClip, sideways, assembled, 2 piece

**Identification Plate Position** none

**Variant** Inside Serrated

**Short Description** Cable Tie and Edge Clip, 50lb, 8.0" Long, EC23, Panel Thickness .12"-.24", PA66UV, Black, 100/bag

## Product Dimensions

**Minimum Tensile Strength (imperial)** 50.0 lbs

**Length L (imperial)** 8.0 "

**Length L (metric)** 200 mm

**Length L2 (imperial)** 0.58 "

**Length L2 (metric)** 14.8 mm

**Width W (imperial)** 0.18 "

**Width W (metric)** 4.6 mm

**Width W2 (imperial)** 0.63 "

**Width W2 (metric)** 16.0 mm

**Height H (imperial)** 0.05 "

**Height H (metric)** 1.2 mm

**Height H2 (imperial)** 0.57 "

**Height H2 (metric)** 14.6 mm

**Bundle Diameter min (imperial)** 0.06 "

**Bundle Diameter min (metric)** 1.0 mm

**Bundle Diameter max (imperial)** 2.0 "

**Bundle Diameter max (metric)** 45.0 mm

**Panel Thickness max. (imperial)** 0.24 "

**Panel Thickness max. (metric)** 6.00 mm

**Panel Thickness min. (imperial)** 0.12 "

Panel Thickness min. (metric) 3.00 mm

---

## Logistics and Packaging

---

**Quantity per** bag  
**Package Quantity** 100

---

## Material and Specifications

---

**Material** Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)  
Polyamide 6.6 UV-stabilized (PA66UV)

**Material Shortcut** PA66UV  
PA66HIRHSUV

**Material Cable Tie** Polyamide 6.6 UV-stabilized (PA66UV)

**Material Edge Clip** Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)  
Stainless Steel (SS)

**Flammability** UL94 HB  
UL94 V2

**Operating Temperature** -40 °F to +230 °F (-40 °C to +110 °C)  
-40 °F to +185 °F (-40 °C to +85 °C)

**ROHS Conformity** Yes