

156-01601



Article Number: 156-01601

Rotatable Cable Tie and Edge Clip, 8.0" Length, Outside Serrated, PA66HS, Black, 500/bag

 RoHS

Base Data

Local Order Number	156-01601
Type	CBTO50R
Color	Black (BK)
Features and Benefits	• Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole. • Edge Clip provides low insertion force and high extraction force ideal for assembly environments. • Cable tie is both rotatable and outside serrated to reduce bundle chafing.
Product Description	The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.
Fixation Method (FF)	Edge Clips with tie
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Variant	Inside Serrated
Short Description	Rotatable Cable Tie and Edge Clip, 8.0" Length, Outside Serrated, PA66HS, Black, 500/bag

Product Dimensions

Minimum Tensile Strength (imperial)	50.0 lbs
Minimum Tensile Strength (N)	225 N
Length L (imperial)	8.0 "
Length L (metric)	202 mm
Length L2 (imperial)	0.52 "
Length L2 (metric)	13.2 mm
Width W (imperial)	0.18 "
Width W (metric)	4.6 mm
Cable Tie Width Max (imperial)	0.18 "
Cable Tie Width max. (metric)	4.6 mm
Width W2 (imperial)	0.5 "
Width W2 (metric)	12.0 mm
Height H (imperial)	0.05 "
Height H (metric)	1.2 mm
Height H2 (imperial)	0.6 "
Height H2 (metric)	15.2 mm
Bundle Diameter min (imperial)	0.08 "
Bundle Diameter min (metric)	2.0 mm
Bundle Diameter max (imperial)	1.9 "

Bundle Diameter max (metric)	47.0 mm
Panel Thickness max. (imperial)	0.12 "
Panel Thickness max. (metric)	3.0 mm
Panel Thickness min. (imperial)	0.04 "
Panel Thickness min. (metric)	1.0 mm
Thickness T (imperial)	0.05 "
Thickness T (Metric)	1.2 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	500
Carton Quantity	4000 Pieces
Weight (Metric)	4.5 kg

Material and Specifications

Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
Material Shortcut	PA66HS PA66HIRHS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Material Edge Clip	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
Flammability	UL94 V2
Operating Temperature	-40 °F to +221 °F (-40 °C to +105 °C)
ROHS Conformity	Yes