

181-00581



Article Number: 181-00581

Slotted Wall Wiring Duct, 2" X 3", Adhesive, PVC, Black, 120ft/Carton



Base Data

Local Order Number 181-00581

Type SLA2X3

Color Black (BK)

- Features and Benefits**
- Strong fingers prevent unwanted breaking.
 - Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct.
 - Restricted opening design in the finger of the duct helps keep wires in place.
 - Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.

Product Description Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and "Ts".

Short Description Slotted Wall Wiring Duct, 2" X 3", Adhesive, PVC, Black, 120ft/Carton

Product Dimensions

Length L (imperial) 6.0 ft

Length L (metric) 1.83 m

Width W (imperial) 2.02 "

Width W (metric) 51.3 mm

Width W2 (imperial) 2.0 "

Width W2 (metric) 50.8 mm

Width W3 (imperial) 0.4 "

Width W3 (metric) 10.2 mm

Width W4 (imperial) 1.0 "

Width W4 (metric) 25.4 mm

Width W5 (imperial) 2.6 "

Width W5 (metric) 66.0 mm

Width W6 (imperial) 0.5 "

Width W6 (metric) 12.7 mm

Height H (imperial) 3.06 "

Height H (metric) 77.7 mm

Mounting Hole Centers (imperial) 4.0 "

Mounting Hole Centers (metric) 101.6 mm

Logistics and Packaging

Quantity per carton

Package Quantity (imperial) 120 ft

Package Quantity 36.6 m

Carton Quantity 120 ft

Material and Specifications

Material Polyvinylchloride (PVC)

Material Shortcut PVC

CSA Certified Yes

Flammability self-extinguishing

Operating Temperature +122 °F (+50 °C)

ROHS Conformity Yes

Certification / Specification CSA
UL

UL Listed (US and Canada) No

UL Recognized (US and Canada) No

UL Recognized (US) Yes